

2-2055713-0

**MPO Trunk Cable, 2x12 fiber, singlemode, MPO female-female, LSZH, straight, 20 m**

## Body Features

Cable Color	Yellow
Boot Color (End A)	Green
Boot Color (End B)	Green
Boot Type (End B)	Standard
Connector Color (End A)	Green
Connector Color (End B)	Green

## Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	20.00 m   65.62 ft
Cable Outer Diameter	.315 in   8 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OS2
Fiber Diameter	9/125 µm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube, gel-filled
Optical Mode	Singlemode
Polarity	Straight

## Signal Characteristics

Return Loss, minimum	35 dB
----------------------	-------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

2-2055713-0

---

## \* Footnotes

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---