



2-2160135-0

MPOptimate® MPO Trunk Cable, Multimode, MPO to MPO, aqua, 20 m

Body Features

Cable Color Aqua

Configuration Features

Number of Fibers 12
Number of Connectors (End A) 1
Number of Connectors (End B) 1

Dimensions

Assembly Length 20.00 m | 65.62 ft

Product Availability

Region Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Product Type Trunk cable
System AMP NETCONNECT | MPOptimate®
Connector Type (End A) MPO
Connector Type (End B) MPO
Fiber Type OM3
Fiber Diameter 50/125 μ m
Optical Mode Multimode

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length Assembly length includes the breakout lengths