

2-599622-3

Fiber Optic Cable, 4-fiber, OM3, 2000 m, aqua

Body Features

Cable Color	Aqua
Cable Construction	1 x 4
Bend Radius (Installation)	130.05 mm 5.12 in
Bend Radius (Long Term)	80.00 mm 3.15 in
Tensile Strength (Installation)	1249.95 N 281.00 lbf
Tensile Strength (Long Term)	650.00 N 146.13 lbf
Weight (Nominal)	48.0 kg/km

Configuration Features

Number of Fibers	4
------------------	---

Dimensions

Length	1999.99 m 6561.66 ft
Outside Diameter	6.40 mm 0.25 in

Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

Operation/Application

Environment	Outdoor
-------------	---------

Product Availability

Region	Asia Australia/New Zealand EMEA
--------	-------------------------------------

Product Type Features

Product Type	Cable
Fiber Type	OM3
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 µm
System	AMP NETCONNECT

Signal Characteristics

Attenuation, maximum (1300nm)	0.70 dB/km
Attenuation, maximum (850nm)	3.50 dB/km

Usage Conditions

Operating Temperature Range	-20 – 70 °C -4 – 158 °F
-----------------------------	---------------------------

2-599622-3

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant