

2-599629-3

Indoor/Outdoor Loose Tube Cable, 48-fiber, OM3, LSZH, dielectric, aqua

Body Features

Cable Color	Aqua
Cable Construction	4 x 12
Bend Radius (Installation)	228.60 mm 9.00 in
Bend Radius (Long Term)	169.93 mm 6.69 in
Tensile Strength (Installation)	996.40 N 224.00 lbf
Tensile Strength (Long Term)	600.00 N 134.89 lbf
Weight (Nominal)	105.0 kg/km

Configuration Features

Number of Fibers	48
Number of Fillers	4

Dimensions

Length	1999.99 m 6561.66 ft
Outside Diameter	11.50 mm 0.45 in

Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

Operation/Application

Environment	Indoor/Outdoor
-------------	----------------

Product Availability

Region	Asia Australia/New Zealand EMEA
--------	-------------------------------------

Product Type Features

Product Type	Cable
Fiber Type	OM3
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 µm
System	AMP NETCONNECT

Signal Characteristics

Attenuation, maximum (1300nm)	1.00 dB/km
Attenuation, maximum (850nm)	3.50 dB/km

Usage Conditions

Installation Temperature Range	-5 – 50 °C
--------------------------------	------------

2-599629-3

Operating Temperature Range -10 – 70 °C | 14 – 158 °F

Storage Temperature Range -20 – 70 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant