

**2111015-1****Faceplate Kit, labeled, 2-gang, 12 port, vertical orientation, almond**

- Engineered for residential and commercial applications from classrooms and hospitals to offices and homes
- Labeling models feature mold-over icon and leveling and convex labels for maximum visibility in low density areas
- Wide range of port configurations, including single gang in 1-, 2-, 3-, 4- and 6-port and double gang in 6-, 8- and 12-port

Body Features

Color	Almond
Material	Thermoplastic

Configuration Features

Number of Ports	12
Outlet Size	2-gang
Preloaded	No

Dimensions

Depth	5.588 mm 0.220 in
Height	114.300 mm 4.500 in
Width	115.824 mm 4.560 in

Identification Marking

Label Area	Yes
Marking Options	Icon Wheel Label

Industry Standards

Approved Standards	IEC 60603-7
--------------------	-------------

Mechanical Attachment

Mounting Style	Flush Mount
Mounts To	Standard ANSI/NEMA outlet boxes with 3.28 in centerline mounting

Operation/Application

Accepts	SL Series Inserts SL Series Jacks
---------	-------------------------------------

Packaging Features

Includes	Faceplate (1) Label (4) Label cover (4) Mounting screw (4)
Packaging Method	Bag
Packaging Quantity	1

2111015-1

Product Availability

Region Australia/New Zealand | Latin America | North America

Product Type Features

Product Type	Faceplate
System	AMP NETCONNECT E Series KL Series
Orientation	Straight Vertical

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant