



2111022-2

Faceplate Kit, non-labeled, 1-gang, 2 port, vertical orientation, black

- Engineered for residential and commercial applications from classrooms and hospitals to offices and homes
- Labeling models feature mold-over icon and leveling and convex labels for maximum visibility in low density areas
- Wide range of port configurations, including single gang in 1-, 2-, 3-, 4- and 6-port and double gang in 6-, 8- and 12-port

Body Features

Color	Black
Material	Thermoplastic

Configuration Features

Number of Ports	2
Outlet Size	1-gang
Preloaded	No

Dimensions

Depth	5.588 mm 0.220 in
Height	114.300 mm 4.500 in
Width	69.850 mm 2.750 in

Identification Marking

Label Area	No
Marking Options	Label or Cover

Industry Standards

Approved Standards	IEC 60603-7
--------------------	-------------

Mechanical Attachment

Mounting Style	Flush Mount
Mounts To	Standard ANSI/NEMA outlet boxes with 3.28 in centerline mounting

Operation/Application

Accepts	SL Series Inserts SL Series Jacks
---------	-------------------------------------

Packaging Features

Includes	Faceplate (1) Label (2) Label cover (2) Mounting screw (2)
Packaging Method	Bag
Packaging Quantity	1

2111022-2

Product Availability

Region Asia | Australia/New Zealand | Latin America | North America

Product Type Features

Product Type Faceplate
System AMP NETCONNECT | E Series | KL Series
Orientation Straight | Vertical

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant