

2111475-7

E Series Modular Jack, 8-position, category 6, unshielded UTP, RJ45, T568A/T568B wiring, red

Body Features

110 Block Material	Polycarbonate
--------------------	---------------

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Cable Diameter (Max)	5.8 mm 0.2 in
Insulated Conductor Outside Diameter	0.057 in 1.45 mm
Solid Wire Range	.51 mm ² .65 mm ² 22 AWG 24 AWG
Stranded Wire Range	.14 mm ² .2 mm ² 24 AWG 26 AWG

Housing Features

Housing Color	Red
Housing Material	Polycarbonate

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Mechanical Attachment

Mounting Type	KL Series Faceplate Panel Mount
---------------	-----------------------------------

Packaging Features

Packaging Method	Poly Bag
------------------	----------

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Modular Jack
Performance Category	Category 6
Shielded	No
Connector Style	Jack

2111475-7

Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant