



2111570-1

AMP-TWIST Modular Patch Panel, category 6A, U/UTP, class EA, unshielded, flat, 24-port, 1U, black

## Body Features

Color	Black
-------	-------

## Configuration Features

Custom Configurable	No
Front Connector Type	RJ45
Number of Rear Connectors	24
Preloaded	No

## Dimensions

Rack Width	482.60 mm   19.00 in
------------	----------------------

## Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

## Product Type Features

Product Type	Patch Panel
System	AMP-TWIST
Panel Type	Patch Panel
Product Category	RJ45 Patch Panel
Rack Units	1.0
Cable Type	UTP
Performance Category	Category 6A
Shielded	No

## Signal Characteristics

Ethernet Speed	10 Gb/s
----------------	---------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant