



2153046-1

MRJ21™ XG Flush Mount Patch Panel, 48 RJ45 ports, 12 MRJ21™ plugs, straight, 1 RU for 10 GbE, black

Body Features

Color	Black
RAL Color	RAL 9005

Configuration Features

Custom Configurable	No
Front Connector Type	RJ45
Number of Rear Connectors	12
Port Capacity	48
Preloaded	No
Rear/Far End Connector Type	MRJ21™

Dimensions

Rack Width	482.60 mm 19.00 in
------------	----------------------

Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

Operation/Application

AMPTRAC Enabled	No
-----------------	----

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Patch Panel
System	AMP NETCONNECT MRJ21™
Panel Type	Patch Panel
Product Category	MRJ21™ Patch Panel
Rack Units	1.0
Performance Category	Category 6A
Profile	Flat
Rack-Mounted	Yes
Shielded	Yes

Signal Characteristics

Ethernet Speed	10 Gb/s
----------------	---------

2153046-1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant