

2160040-2

Fiber Optic Pigtail, OM4, LC-pigtail 900 µm, LSZH, 2 m

Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Type (End A)	Standard
Connector Color (End A)	Beige

Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

Dimensions

Assembly Length	2.00 m 6.56 ft
Cable Outer Diameter	.90 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Pigtail
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM4
Fiber Diameter	50/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Optical Mode	Multimode

Signal Characteristics

Return Loss, minimum	35 dB
----------------------	-------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

2160040-2

Assembly Length

Assembly length includes the breakout lengths