

219420-1

**Copper Cable, category 5e, 4 pair, FTP, LSZH, 24 AWG solid, 305 m reel, white**

## Body Features

Jacket Material	LSZH
Jacket Color	White
Conductor Material	Copper
Insulation Material	PE
Shield Material	Aluminum
Shield Type	Overall foil

## Configuration Features

Number of Pairs	4
Number of Conductors	8

## Dimensions

Overall Outside Diameter	6.200 mm   0.244 in
Conductor Diameter	.485 – .546 mm
Length	305.00 m   1000.66 ft
Wire Diameter	5.195 mm   0.205 in
Wire Size (CMA)	.205 mm <sup>2</sup>   24 AWG

## Electrical Characteristics

Voltage Rating	40 Vdc
----------------	--------

## Electrical Specifications

ANSI/TIA Category	5e
-------------------	----

## General Specifications

Cable Type	F/UTP (shielded)
------------	------------------

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Packaging Features

Packaging Method	Reel
Packaging Quantity	1000

## Product Availability

Region	EMEA
--------	------

## Product Type Features

Cable Style	Simplex
-------------	---------

219420-1

Cable Type	Twisted Pair
Product Classification	Cable - ISO/IEC Category
Product Type	Cable
Shielded	Yes
System	AMP NETCONNECT
Wire/Cable Type	Twisted Pair

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant