

219584-2

Horizontal Copper Cable, category 6, 4 pair, UTP, PVC, 23 AWG, 305 m reel-in-box, white

## Body Features

Jacket Material	PVC
Jacket Color	White
Conductor Material	Copper
Insulation Material	PE

## Configuration Features

Number of Pairs	4
Number of Conductors	8

## Dimensions

Overall Outside Diameter	5.700 mm		0.224 in
Conductor Diameter	.485 – .546 mm		
Length	305.00 m		1000.66 ft
Wire Diameter	5.495 mm		0.216 in
Wire Size (CMA)	.205 mm <sup>2</sup>		24 AWG

## Electrical Specifications

ANSI/TIA Category	6
-------------------	---

## General Specifications

Cable Type	U/UTP (unshielded)
------------	--------------------

## Industry Standards

Flammability Rating	PVC
---------------------	-----

## Packaging Features

Packaging Method	Reel-in-a-Box
Packaging Quantity	1000

## Product Availability

Region	EMEA
--------	------

## Product Type Features

Cable Style	Simplex
Cable Type	Twisted Pair
Product Classification	Cable - ISO/IEC Category
Product Type	Cable
Shielded	No
System	AMP NETCONNECT
Wire/Cable Type	Twisted Pair

219584-2

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant