

**219839-8****RJ45 Patch Cord, category 5, shielded, gray, 5 m**

## Body Features

Cable Color	Gray
Shield Style	F/UTP
Conductor Material	Stranded tinned copper
Conductor Type	Stranded

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0

## Dimensions

Length	5.00 m   16.40 ft
Overall Outside Cable Diameter	5.400 mm   0.213 in
Wire Size (CMA)	.129 mm <sup>2</sup>   26 AWG

## Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

## Operation/Application

Halogen Free	No
--------------	----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia
--------	------

## Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 5e

# Product Specifications



2198398

Cable Assembly Category	Industry Standard
Shielded	Yes

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant