



2291217-5

**KJ Series Modular Jack, category 5e, orange**

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	1.27 µm

## Dimensions

Insulation Diameter (Max)	1.27 mm   0.05 in
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

## Housing Features

Housing Color	Orange
Housing Material	Polycarbonate

## Industry Standards

Approved Standards	ANSI/TIA-568-C.2   ISO/IEC 11801
UL Flammability Rating	UL 94V-0

## Mechanical Attachment

Mount Cutout Dimensions	.582 x .760 in   14.79 x 19.30 mm
Mounting Type	Faceplate Mount   Panel Mount
Mounts To	Hubbell Faceplate   KJ Series   Leviton Faceplate   Panduit Faceplate

## Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

2291217-5

## Product Type Features

Product Type	Modular Jack
Performance Category	Category 5e
Shielded	No
System	AMP NETCONNECT   KJ Series
Applies To	Faceplate   Panel
Dust Cover	Without
Jack Type	RJ45
Strain Relief	Yes

## Termination Features

Termination Method	Insulation Displacement Connector (IDC)
Termination Style	110 Style Punch-Down   SL Termination Tool

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant