

**2291217-9****KJ Series Modular Jack, category 5e, green**

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	1.27 µm

Dimensions

Insulation Diameter (Max)	1.27 mm 0.05 in
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

Housing Features

Housing Color	Green
Housing Material	Polycarbonate

Industry Standards

Approved Standards	ANSI/TIA-568-C.2 ISO/IEC 11801
UL Flammability Rating	UL 94V-0

Mechanical Attachment

Mount Cutout Dimensions	.582 x .760 in 14.79 x 19.30 mm
Mounting Type	Faceplate Mount Panel Mount
Mounts To	Hubbell Faceplate KJ Series Leviton Faceplate Panduit Faceplate

Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

2291217-9

Product Type Features

Product Type	Modular Jack
Performance Category	Category 5e
Shielded	No
System	AMP NETCONNECT KJ Series
Applies To	Faceplate Panel
Dust Cover	Without
Jack Type	RJ45
Strain Relief	Yes

Termination Features

Termination Method	Insulation Displacement Connector (IDC)
Termination Style	110 Style Punch-Down SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant