

279261-1

Copper Cable, category 3, 25 pair, U/UTP Cable, CM rated, 500 m, white

Body Features

Jacket Material	PVC
Jacket Color	White
Conductor Material	Solid copper

Configuration Features

Number of Pairs	25
Number of Conductors	50

Dimensions

Length	500.00 m 1640.42 ft
Wire Size (CMA)	.205 mm ² 24 AWG

Electrical Specifications

ANSI/TIA Category	3
-------------------	---

General Specifications

Cable Type	U/UTP (unshielded)
------------	--------------------

Industry Standards

Flammability Rating	CM
---------------------	----

Outline Drawing

Packaging Features

Packaging Method	Reel
------------------	------

Product Availability

Region	Australia/New Zealand
--------	-----------------------

Product Type Features

Cable Style	Multi-Pair
Product Type	Cable
Shielded	No
System	AMP NETCONNECT
Wire/Cable Type	Twisted Pair

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant