

3-2055713-0

MPO Trunk Cable, 2x12 fiber, singlemode, MPO female-female, LSZH, straight, 30 m

Body Features

Cable Color	Yellow
Boot Color (End A)	Green
Boot Color (End B)	Green
Boot Type (End B)	Standard
Connector Color (End A)	Green
Connector Color (End B)	Green

Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	30.00 m 98.43 ft
Cable Outer Diameter	.315 in 8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OS2
Fiber Diameter	9/125 µm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube, gel-filled
Optical Mode	Singlemode
Polarity	Straight

Signal Characteristics

Return Loss, minimum	35 dB
----------------------	-------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

3-2055713-0

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---