



3-2160135-4

MPOptimate® Trunk Cable, 12 fiber, female-female, OM3, straight, 34 m

Body Features

Cable Color	Aqua
Boot Color (End A)	Black
Boot Type (End A)	Round
Connector Color (End A)	Beige
Connector Color (End B)	Green

Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1

Dimensions

Assembly Length	34.00 m 111.55 ft
Cable Outer Diameter	.126 in 3.2 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Thermoplastic
Optical Mode	Multimode
Polarity	Straight

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications



3-2160135-4

RoHS 2011/65/EU

Compliant

* **Footnotes**

Assembly Length	Assembly length includes the breakout lengths
-----------------	---