



3-2160135-5

**MPOptimate® Trunk Cable, 12 fiber, female-female, OM3, straight, 35 m**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Black
Boot Type (End A)	Round
Connector Color (End A)	Beige
Connector Color (End B)	Green

## Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1

## Dimensions

Assembly Length	35.00 m   114.83 ft
Cable Outer Diameter	.126 in   3.2 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT   MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Thermoplastic
Optical Mode	Multimode
Polarity	Straight

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

---

3-2160135-5

RoHS 2011/65/EU

Compliant

---

## \* **Footnotes**

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---