



3-2160608-5

MPOptimate® Trunk Cable, 24 fiber, MPO female, OM4, straight, 35 m

Body Features

Cable Color	Aqua
-------------	------

Configuration Features

Number of Fibers	24
Number of Connectors (End A)	1
Number of Connectors (End B)	1

Dimensions

Assembly Length	35.00 m 114.83 ft
-----------------	---------------------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM4
Fiber Diameter	50/125 µm
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---