

**3-553079-4****Undercarpet Flat Copper Cable, 3 conductors, 12 AWG, shielded, 100 ft, white/green/black**

## Body Features

Color	White/Green/Black
Conductor Color	White/Green/Black
Conductor Material	Copper
Ground Type	Standard
Insulation Material	PVC/Polyester

## Configuration Features

Configuration	Power
Number of Conductors	3

## Dimensions

Height	1.300 mm   0.051 in
Length	30.48 m   100.00 ft
Width	70.570 mm   2.778 in
Wire Size (CMA)	12 AWG   3.31 mm <sup>2</sup>

## Electrical Characteristics

Current Rating	20 A
Voltage Rating	300 V

## Housing Features

Centerline	23.495 mm   0.925 in
------------	----------------------

## Industry Standards

Standards Compliance	CSA   UL
UL File Number	E73212

## Other

Comment	Undercarpet Power Cable
---------	-------------------------

## Packaging Features

Packaging Method	Reel
------------------	------

## Product Availability

Region	Latin America   North America
--------	-------------------------------

3-553079-4

## Product Type Features

---

Product Type	Cable
Cable Type	FCC
Product Category	Power Cable
Product Classification	Cable - FCC
Shielded	Yes
System	AMP NETCONNECT

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant