

**3-553239-3****Undercarpet Flat Copper Cable, 5 conductors, 12 AWG, shielded, 50 ft, white/green/black**

Body Features

Color	White/Green/Black/Blue/Red
Conductor Color	White/Green/Black/Blue/Red
Conductor Material	Copper
Ground Type	Standard
Insulation Material	PVC/Polyester

Configuration Features

Configuration	Power
Number of Conductors	5

Dimensions

Height	1.300 mm 0.051 in
Length	15.25 m 50.03 ft
Width	117.348 mm 4.620 in
Wire Size (CMA)	12 AWG 3.31 mm ²

Electrical Characteristics

Current Rating	20 A
Voltage Rating	300 V

Housing Features

Centerline	23.495 mm 0.925 in
------------	----------------------

Industry Standards

Standards Compliance	CSA UL
UL File Number	E73212

Other

Comment	Undercarpet Power Cable
---------	-------------------------

Packaging Features

Packaging Method	Reel
------------------	------

Product Availability

Region	Latin America North America
--------	-------------------------------

3-553239-3

Product Type Features

Product Type	Cable
Cable Type	FCC
Product Category	Power Cable
Product Classification	Cable - FCC
Shielded	Yes
System	AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant