

336488-1

**RJ45 Patch Cord, category 6A, S/FTP, LSZH, stranded, shielded, white, 1 m**

## Body Features

Cable Color	White
Shield Style	S/FTP
Conductor Material	Copper

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

## Dimensions

Length	1.00 m   3.28 ft
Overall Outside Cable Diameter	5.900 mm   0.232 in
Wire Size (CMA)	.129 – .205 mm <sup>2</sup>   26 – 24 AWG

## Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

## Operation/Application

Halogen Free	Yes
--------------	-----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT   AMP-TWIST
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	4P AMP-TWIST Plug
Performance Category	Category 6A
Cable Assembly Category	Industry Standard
Shielded	Yes

## Usage Conditions

Operating Temperature Range	-20 – 60 °C
-----------------------------	-------------

## Regulatory Compliance/Certifications

# Product Specifications



---

336488-1

---

**Agency**

RoHS 2011/65/EU

---

**Classification**

Compliant