

**4-1206480-4****Fiber Optic Termination Panel, 1U, 19 in, multimode, 24 ST/PC, sliding, black**

## Body Features

Cable Entry	Rear
Cable Exit	Rear
Chassis Color	Black
Finish	Powder coated

## Configuration Features

Number of Ports	24
Front Connector Type	ST/UPC
Splice Chip Type	Mechanical
Configuration	Adapters only
Number of Fibers	24
Port Style	Simplex
Splice Capacity	4

## Dimensions

Height	44.450 mm   1.750 in
Width	482.600 mm   19.000 in

## Packaging Features

Includes	Installation Instruction   Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

## Product Availability

Region	EMEA
--------	------

## Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Optical Mode	Multimode

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant