

**4-1671130-8****Fiber Optic Termination Panel, 1 RU, 19 in, 24 LC/UPC duplex, gray**

Body Features

Cable Entry	Rear
Cable Exit	Rear
Chassis Color	Gray
Finish	Powder coated

Configuration Features

Number of Ports	24
Front Connector Type	LC/UPC
Configuration	Adapters only
Number of Fibers	24
Number of Splice Organizer Trays	2
Port Style	Duplex

Dimensions

Height	44.450 mm 1.750 in
Width	482.600 mm 19.000 in

Other

Comment	2 rear cable entries Supplied with ANT splicing trays
---------	---

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	EMEA
--------	------

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant