



4-2055578-6

**MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 46 m, aqua**

## Body Features

Cable Color	Aqua
-------------	------

## Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	46.00 m   150.92 ft
Cable Outer Diameter	.315 in   8 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT   MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM4
Fiber Diameter	50/125 µm
Optical Mode	Multimode
Polarity	Straight

## Regulatory Compliance/Certifications

<b>Agency</b> RoHS 2011/65/EU	<b>Classification</b> Compliant
----------------------------------	------------------------------------

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---