



4-2055611-0

MPOptimate® Trunk Cable, 12 fiber, multimode OM3, MPO-MPO female, XG, straight, 40 m, aqua

Body Features

| | |
|-------------------------|-------|
| Cable Color | Aqua |
| Boot Color (End A) | Black |
| Boot Color (End B) | Black |
| Boot Type (End A) | Round |
| Boot Type (End B) | Round |
| Connector Color (End A) | Beige |
| Connector Color (End B) | Beige |

Configuration Features

| | |
|------------------------------|----|
| Number of Fibers | 12 |
| Number of Connectors (End A) | 1 |
| Number of Connectors (End B) | 1 |

Dimensions

| | |
|----------------------|---------------------|
| Assembly Length | 40.00 m 131.23 ft |
| Cable Outer Diameter | .252 in 6.4 mm |

Industry Standards

| | |
|---------------------|------|
| Flammability Rating | LSZH |
|---------------------|------|

Product Availability

| | |
|--------|------------------------------|
| Region | Australia/New Zealand EMEA |
|--------|------------------------------|

Product Type Features

| | |
|------------------------|------------------------------|
| Product Type | Trunk cable |
| System | AMP NETCONNECT MPOptimate® |
| Connector Type (End A) | MPO |
| Connector Type (End B) | MPO |
| Fiber Type | OM3 |
| Fiber Diameter | 50/125 µm |
| Ferrule Material | Thermoplastic |
| Fiber Cable Buffering | Loose tube, gel-filled |
| Optical Mode | Multimode |
| Polarity | Straight |

4-2055611-0

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length

Assembly length includes the breakout lengths