



406363-1

AMP CO™ Patch Panel, category 5e, 16-port, 2 RU, unshielded, 110 termination, white

NOTE: Inserts sold separately

Configuration Features

Custom Configurable	No
Front Connector Type	RJ45
Port Capacity	16

Dimensions

Height	88.900 mm		3.500 in
Rack Width	482.60 mm		19.00 in

Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

Operation/Application

AMPTRAC Enabled	No
-----------------	----

Other

Comment	ACO inserts sold separately
UCP Product	No

Product Availability

Region	Asia		Latin America		North America
--------	------	--	---------------	--	---------------

Product Type Features

Product Type	Patch Panel
System	AMP CO™ AMP NETCONNECT
Panel Type	Patch Panel
Product Category	ACO Patch Panel
Rack Units	2.0
Performance Category	Category 5e
Profile	Flat
Rack-Mounted	Yes
Shielded	No

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Not Compliant