



5-1375204-2

**RJ45 Modular Plug Kit, 8-position, category 6**

## **OBSOLETE**

### **Replaced By:**

MP-6S-B-5  
6-2111979-2

Modular Plug Kit, category 6, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 500/bag

## **Body Features**

Conductor Type	Solid
Shield Material	Brass
Shield Plating Material	Nickel

## **Configuration Features**

Number of Positions	8
Keyed	No

## **Contact Features**

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

## **Dimensions**

Cable Jacket Outside Diameter Range	0.197–0.237 in   0.2–0.236 in   5–6 mm
Conductor Wire Size	24–23 AWG
Insulated Conductor Outside Diameter	0.035–0.04 in   0.89–1 mm

## **Housing Features**

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## **Industry Standards**

UL Flammability Rating	UL 94V-2
------------------------	----------

## **Product Availability**

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## **Product Type Features**

Performance Category	Category 6
Connector Style	Plug
Latch Style	Standard

5-1375204-2

Product Type	Connector
Shielded	Shielded/Unshielded (Cable Dependent)
System	AMP NETCONNECT

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant