



5-1375204-3

RJ45 Modular Plug, category 6, 8-position, solid wire

OBSOLETE

Replaced By:

MP-6S-B-1
6-2111979-3

Modular Plug Kit, category 6, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 100/bag

Body Features

Conductor Type	Solid
Shield Material	Brass
Shield Plating Material	Nickel

Configuration Features

Number of Positions	8
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.197–0.237 in 0.2–0.236 in 5–6 mm
Conductor Wire Size	24–23 AWG
Insulated Conductor Outside Diameter	0.035–0.04 in 0.89–1 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Performance Category	Category 6
Connector Style	Plug
Latch Style	Standard

5-1375204-3

Product Type

Connector

Shielded

Shielded/Unshielded (Cable Dependent)

System

AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant