



5-2055711-5

MPO Trunk Cable, 12 fiber, singlemode, MPO female-female, LSZH, straight, 55 m

Body Features

Cable Color	Yellow
Boot Color (End A)	Black
Boot Color (End B)	Black
Boot Type (End B)	Standard
Connector Color (End A)	Green
Connector Color (End B)	Green

Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	55.00 m 180.45 ft
Cable Outer Diameter	.251 in 6.4 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OS2
Fiber Diameter	9/125 μm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube
Optical Mode	Singlemode
Polarity	Straight

Signal Characteristics

5-2055711-5

Return Loss, minimum 35 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length Assembly length includes the breakout lengths