



5-2160135-0

**MPOptimate® Trunk Cable, 12 fiber, female-female, OM3, straight, 50 m**

## Body Features

|                         |       |
|-------------------------|-------|
| Cable Color             | Aqua  |
| Boot Color (End A)      | Black |
| Boot Type (End A)       | Round |
| Connector Color (End A) | Beige |
| Connector Color (End B) | Green |

## Configuration Features

|                              |    |
|------------------------------|----|
| Number of Fibers             | 12 |
| Number of Connectors (End A) | 1  |
| Number of Connectors (End B) | 1  |

## Dimensions

|                      |                     |
|----------------------|---------------------|
| Assembly Length      | 50.00 m   164.04 ft |
| Cable Outer Diameter | .126 in   3.2 mm    |

## Industry Standards

|                     |      |
|---------------------|------|
| Flammability Rating | LSZH |
|---------------------|------|

## Product Availability

|        |                              |
|--------|------------------------------|
| Region | Australia/New Zealand   EMEA |
|--------|------------------------------|

## Product Type Features

|                        |                              |
|------------------------|------------------------------|
| Product Type           | Trunk cable                  |
| System                 | AMP NETCONNECT   MPOptimate® |
| Connector Type (End A) | MPO                          |
| Connector Type (End B) | MPO                          |
| Fiber Type             | OM3                          |
| Fiber Diameter         | 50/125 µm                    |
| Ferrule Material       | Thermoplastic                |
| Optical Mode           | Multimode                    |
| Polarity               | Straight                     |

## Regulatory Compliance/Certifications

Agency

Classification

---

5-2160135-0

RoHS 2011/65/EU

Compliant

---

## \* **Footnotes**

---

|                 |   |
|-----------------|---|
| Assembly Length | Assembly length includes the breakout lengths |
|-----------------|---|