



5-554169-2

RJ45 Modular Plug Assembly, category 5e, 8-position, unshielded, round cable

OBSOLETE

Replaced By:

MP-88U-R-5
6-557315-2

Modular Plug Kit, 8P/8C, unshielded, round, 5.1 mm max cable jack OD, 8-position, 500/bag

Body Features

Conductor Type Stranded

Configuration Features

Number of Positions 8
Keyed No

Contact Features

Contact Base Material Phosphor bronze
Number of Contacts Loaded 8

Dimensions

Cable Jacket Outside Diameter Range 0.21 in | 5.33 mm
Conductor Wire Size 28-26 AWG
Insulated Conductor Outside Diameter 0.029-0.039 in | 0.74-0.99 mm

Housing Features

Housing Material Glass filled polycarbonate

Industry Standards

UL Flammability Rating UL 94V-2

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Performance Category Category 5
Connector Style Plug
Latch Style Standard
Product Type Connector
Shielded No

5-554169-2

System

AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant