

**5-554170-3****Modular Plug, 8P/8C, unshielded, keyed, round****OBSOLETE****Replaced By:**MP-66U-R-1
6-554710-3Modular Plug, 6P/6C, unshielded, standard body, round, 4.6 mm cable jack OD, 6-position,
category 3, 100/bag**Body Features**

Conductor Type	Stranded
----------------	----------

Configuration Features

Number of Positions	8
Keyed	Yes

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.21 in 5.33 mm
Conductor Wire Size	28-26 AWG
Insulated Conductor Outside Diameter	0.029-0.039 in 0.74-0.99 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Other

Comment	Keyed Modular Plug
---------	--------------------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Performance Category	Category 5
Connector Style	Plug

Product Specifications



5-554170-3

Latch Style	Standard
Product Type	Connector
Shielded	No
System	AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant