

**5-554710-3****Modular Plug Assembly, RJ11, category 3, 6-position, unshielded, round cable****OBSOLETE****This product was discontinued on: April 1, 2016****Replaced By:**MP-66U-R-1  
6-554710-3

Modular Plug, 6P/6C, unshielded, standard body, round, 4.6 mm cable jack OD, 6-position, category 3, 100/bag

**Body Features**

Conductor Type	Stranded
----------------	----------

**Configuration Features**

Number of Positions	6
Keyed	No

**Contact Features**

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	6

**Dimensions**

Cable Jacket Outside Diameter Range	0.18 in   4.58 mm
Conductor Wire Size	28–26 AWG
Insulated Conductor Outside Diameter	0.029–0.039 in   0.74–0.99 mm

**Housing Features**

Housing Material	Glass filled polycarbonate
------------------	----------------------------

**Industry Standards**

UL Flammability Rating	UL 94V-2
------------------------	----------

**Product Availability**

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

**Product Type Features**

Performance Category	Category 3
Connector Style	Plug
Latch Style	Standard
Product Type	Connector

# Product Specifications



5-554710-3

Shielded	No
System	AMP NETCONNECT

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant