



5-554720-2

**RJ45 Modular Plug Assembly, category 5e, unshielded, 8-position, 24–26 AWG, solid wire**

## **OBSOLETE**

**This product was discontinued on: April 1, 2016**

### **Replaced By:**

MP-88U-F-5  
6-554720-2

Modular Plug Kit, 8P/8C, unshielded, flat oval, 2.54 x 8.89 mm max cable jack OD, 8-position, 500/bag

## **Body Features**

Conductor Type	Solid
----------------	-------

## **Configuration Features**

Number of Positions	8
Keyed	No

## **Contact Features**

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

## **Dimensions**

Cable Jacket Outside Diameter Range	0.1–0.35 in   2.54–8.89 mm
Conductor Wire Size	26–24 AWG
Insulated Conductor Outside Diameter	0.035–0.039 in   0.89–0.99 mm

## **Housing Features**

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## **Industry Standards**

UL Flammability Rating	UL 94V-2
------------------------	----------

## **Product Availability**

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## **Product Type Features**

Performance Category	Category 5
Connector Style	Plug
Latch Style	Standard
Product Type	Connector

5-554720-2

Shielded	No
System	AMP NETCONNECT

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant