



5-557315-3

RJ45 Plug, category 5E, 8-position, unshielded, round cable, solid wire

OBSOLETE

Replaced By:

MP-88U-R-1
6-557315-3

Modular Plug Kit, 8P/8C, unshielded, round, 5.1 mm max cable jack OD, 8-position, 100/bag

Body Features

Conductor Type	Solid
----------------	-------

Configuration Features

Number of Positions	8
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.2 in 5.08 mm
Conductor Wire Size	26-24 AWG
Insulated Conductor Outside Diameter	0.029-0.039 in 0.74-0.99 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Performance Category	Category 5
Connector Style	Plug
Latch Style	Standard
Product Type	Connector
Shielded	No

5-557315-3

System

AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant