

**5-569032-3****Modular Plug Assembly, RJ11, category 3, unshielded, 6-position, solid****OBSOLETE****Replaced By:**

MP-66U-R-1

6-554710-3

Modular Plug, 6P/6C, unshielded, standard body, round, 4.6 mm cable jack OD, 6-position, category 3, 100/bag

Body Features

| | |
|----------------|-------|
| Conductor Type | Solid |
|----------------|-------|

Configuration Features

| | |
|---------------------|----|
| Number of Positions | 6 |
| Keyed | No |

Contact Features

| | |
|---------------------------|-----------------|
| Contact Base Material | Phosphor bronze |
| Number of Contacts Loaded | 6 |

Dimensions

| | |
|--------------------------------------|-------------------------------|
| Cable Jacket Outside Diameter Range | 0.179 in 4.57 mm |
| Conductor Wire Size | 26-24 AWG |
| Insulated Conductor Outside Diameter | 0.029-0.039 in 0.74-0.99 mm |

Housing Features

| | |
|------------------|----------------------------|
| Housing Material | Glass filled polycarbonate |
|------------------|----------------------------|

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|

Product Availability

| | |
|--------|---|
| Region | Asia Australia/New Zealand EMEA Latin America North America |
|--------|---|

Product Type Features

| | |
|----------------------|------------|
| Performance Category | Category 3 |
| Connector Style | Plug |
| Latch Style | Standard |
| Product Type | Connector |
| Shielded | No |

5-569032-3

System

AMP NETCONNECT

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant