



5-569542-3

RJ45 Modular Jack, category 5, shielded, 8-position

OBSOLETE

Replaced By:

MP-88S-F-1
6-569542-3

Modular Plug Kit, 8P/8C, shielded, flat oval, 2.54 x 8.89 mm cable jack OD, 8-position, category 5, 100/bag

Body Features

Conductor Type	Stranded
Shield Material	Copper alloy
Shield Plating Material	Hot-dipped tin

Configuration Features

Number of Positions	8
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.11–0.35 in 2.79–9.02 mm
Conductor Wire Size	28–24 AWG
Insulated Conductor Outside Diameter	0.029–0.039 in 0.74–0.99 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Performance Category	Category 5
Connector Style	Plug
Latch Style	Standard

Product Specifications



5-569542-3

Product Type	Connector
Shielded	Yes
System	AMP NETCONNECT

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant