

**5-641334-3****Modular Plug Assembly, RJ11, category 3, 4 ports, handset, standard latch****OBSOLETE****Replaced By:**MP-44U-F-1  
6-641334-3Modular Plug, 4P/4C, unshielded, headset, flat oval, 2.29 x 4.83 mm cable jack OD, category 3,  
100/bag**Body Features**

Conductor Type	Stranded
----------------	----------

**Configuration Features**

Number of Positions	4
Keyed	No

**Contact Features**

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	4

**Dimensions**

Cable Jacket Outside Diameter Range	0.09–0.19 in   2.29–4.83 mm
Conductor Wire Size	28–26 AWG
Insulated Conductor Outside Diameter	0.039 in   0.99 mm

**Housing Features**

Housing Material	Glass filled polycarbonate
------------------	----------------------------

**Industry Standards**

UL Flammability Rating	UL 94V-2
------------------------	----------

**Product Availability**

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

**Product Type Features**

Performance Category	Category 3
Connector Style	Plug
Latch Style	Standard
Product Type	Connector
Shielded	No

5-641334-3

System

AMP NETCONNECT

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant