

5349567-3

Fiber Optic Patch Cord, multimode, SC to ST, duplex, 2.5 mm tight zipcord, 3 m

OBSOLETE

This product was discontinued on: October 1, 2016

Body Features

Cable Color	Orange
Boot Color (End A)	Red/Black
Boot Color (End B)	Beige
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Black

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	3.00 m 9.84 ft
Cable Outer Diameter	.098 in 2.5 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	SC/UPC
Connector Type (End B)	ST/UPC
Fiber Type	OM2
Fiber Diameter	50/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Easy strip buffer Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode

5349567-3

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---