

5349569-4

Fiber Optic Pigtail, OM2, ST/PC, semi-tight buffer, 2 m, green

## OBSOLETE

This product was discontinued on: October 1, 2016

### Body Features

Cable Color	Green
Boot Color (End A)	Black
Boot Type (End A)	Bare buffer

### Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

### Dimensions

Assembly Length	2.00 m   6.56 ft
Cable Outer Diameter	.035 in   .90 mm

### Industry Standards

Flammability Rating	LSZH
---------------------	------

### Product Availability

Region	Asia   EMEA   Latin America   North America
--------	---

### Product Type Features

Product Type	Pigtail
System	AMP NETCONNECT
Connector Type (End A)	ST/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM2
Fiber Diameter	50/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Optical Mode	Multimode

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

### \* Footnotes

5349569-4

Assembly Length

Assembly length includes the breakout lengths