

5349574-1

Fiber Optic Patch Cord, multimode, 2.5 mm zipcord, ST-ST, duplex, 1 m

OBSOLETE

This product was discontinued on: October 1, 2016

Body Features

Cable Color	Orange
Boot Color (End A)	Red/Black
Boot Color (End B)	Red/Black
Boot Type (End A)	Standard
Boot Type (End B)	Standard

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	1.00 m 3.28 ft
Cable Outer Diameter	.098 in 2.5 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	ST/UPC
Connector Type (End B)	ST/UPC
Fiber Type	OM1
Fiber Diameter	62.5/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Semi-tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode

5349574-1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---