

5349580-1

Fiber Optic Patch Cord, multimode, 2.5 mm zipcord, ST-SC, duplex, 1 m

## OBSOLETE

This product was discontinued on: October 1, 2016

### Body Features

Cable Color	Orange
Boot Color (End A)	Beige
Boot Color (End B)	Red/Black
Boot Type (End A)	Standard
Boot Type (End B)	Standard
Connector Color (End A)	Beige

### Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

### Dimensions

Assembly Length	1.00 m   3.28 ft
Cable Outer Diameter	.098 in   2.5 mm

### Industry Standards

Flammability Rating	LSZH
---------------------	------

### Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

### Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	SC/UPC
Connector Type (End B)	ST/UPC
Fiber Type	OM1
Fiber Diameter	62.5/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Semi-tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode

5349580-1

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---