

5349582-4

Fiber Optic Pigtail, OM1, ST/PC-pigtail, tight buffer, 900 µm, LSZH, 2 m

OBSOLETE

This product was discontinued on: October 1, 2016

Body Features

Cable Color	Blue
Boot Color (End A)	Black
Boot Type (End A)	Bare buffer

Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

Dimensions

Assembly Length	2.00 m 6.56 ft
Cable Outer Diameter	.035 in .90 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia EMEA Latin America North America
--------	---

Product Type Features

Product Type	Pigtail
System	AMP NETCONNECT
Connector Type (End A)	ST/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM1
Fiber Diameter	62.5/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Simplex
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

5349582-4

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---