

**5492123-1****Fiber Optic Connector Kit, SM, SC, 900 µm, 125 µm, 1 piece**

Body Features

Boot Color	Blue
Coating/Buffer Size	900 µm
Epoxyless	No
Ferrule Hole Size	125.5 µm
Protective Cap	Yes
Strain Relief Material	Thermoplastic elastomer (TPE)

Dimensions

Cable Outer Diameter	3 mm
----------------------	------

Housing Features

Housing Color	Blue
Housing Material	Glass filled PBT

Packaging Features

Packaging Method	Carton
Packaging Quantity	1

Product Availability

Region	EMEA
--------	------

Product Type Features

Product Type	Connector
Connector Type	SC UPC
Optical Mode	Singlemode
Cable Type	Buffered Fiber
Connector Style	Simplex
System	AMP NETCONNECT
Connector Design	One-Piece
Ferrule Material	Ceramic
Pre-Polished	No
Strain Relief	Yes

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant