



5501380-6

Fiber Optic ST Kit, ceramic, 140 µm

Body Features

Body Material	Brass
Body Plating Material	Nickel
Boot Color	Black
Boot Material	Thermoplastic elastomer (TPE)
Boot Type	Long
Epoxyless	No
Ferrule Hole Size	140.0 µm

Dimensions

Length	78.00 mm		3.07 in
Outside Cable Diameter (Max)	3.0 mm		0.1 in

Mechanical Attachment

Coupling Nut Material	Zinc
-----------------------	------

Other

Comment	Color dot green.
---------	------------------

Packaging Features

Packaging Method	Bulk
Packaging Quantity	200

Product Availability

Region	Asia		Latin America		North America
--------	------	--	---------------	--	---------------

Product Type Features

Product Type	Connector
Connector Type	ST
Optical Mode	Multimode
Connector Style	Simplex
System	AMP NETCONNECT
Booted	Yes
Ferrule Material	Ceramic
Fiber Diameter	140 µm
Pre-Polished	No

Regulatory Compliance/Certifications

Product Specifications



5501380-6

Agency

RoHS 2011/65/EU

Classification

Compliant