

**5502580-2****Fiber Optic Connector Kit, ST/UPC, singlemode, for 3 mm cable**

Body Features

| | |
|-----------------------|-------------------------------|
| Body Material | Brass |
| Body Plating Material | Nickel |
| Boot Color | Yellow |
| Boot Material | Thermoplastic elastomer (TPE) |
| Boot Type | Bare buffer Short |
| Epoxyless | No |
| Ferrule Hole Size | 126.0 µm |

Dimensions

Outside Cable Diameter (Max) 3.0 mm | 0.1 in

Mechanical Attachment

| | |
|-----------------------|------|
| Coupling Nut Material | Zinc |
|-----------------------|------|

Packaging Features

| | |
|--------------------|------|
| Packaging Method | Bulk |
| Packaging Quantity | 200 |

Product Availability

| | |
|--------|---|
| Region | Asia EMEA Latin America North America |
|--------|---|

Product Type Features

| | |
|------------------|----------------|
| Product Type | Connector |
| Connector Type | ST |
| Optical Mode | Singlemode |
| Connector Style | Simplex |
| System | AMP NETCONNECT |
| Booted | Yes |
| Ferrule Material | Ceramic |
| Fiber Diameter | 126 µm |
| Pre-Polished | No |

Signal Characteristics

| | |
|----------------------|---------|
| Insertion Loss (Max) | 0.30 dB |
|----------------------|---------|

Regulatory Compliance/Certifications

Agency**Classification**

Product Specifications



5502580-2

RoHS 2011/65/EU

Compliant