



5504931-1  
Fiber Optic Connector Kit, SC, MM, 128  $\mu$ m, 2 mm

## Body Features

Boot Color	Beige
Epoxyless	No
Ferrule Hole Size	125.0 $\mu$ m
Protective Cap	Yes
Strain Relief Material	Thermoplastic elastomer (TPE)

## Dimensions

Cable Outer Diameter	2 mm
----------------------	------

## Housing Features

Housing Color	Beige
Housing Material	Glass filled PBT

## Identification Marking

AMP Logo	Yes
----------	-----

## Packaging Features

Packaging Method	Carton
Packaging Quantity	1

## Product Availability

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

Product Type	Connector
Connector Type	SC UPC
Optical Mode	Multimode
Cable Type	Jacketed Cable
Connector Style	Simplex
System	AMP NETCONNECT
Connector Design	One-Piece
Ferrule Material	Ceramic
Pre-Polished	No
Strain Relief	Yes

## Regulatory Compliance/Certifications

### Agency

### Classification

# Product Specifications



---

5504931-1

RoHS 2011/65/EU

Compliant