



552043-2

**PICABOND® Connector, 1000 loose piece, brown**

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

## **OBSOLETE**

This product was discontinued on: **June 1, 2016**

### Replaced By:

552043-4

PICABOND® Connector, 1000 loose piece, mini, brown

## Body Features

Cable Insulation Material	Air Core PIC   Paper or Pulp
Color Code	Brown
Sealant	Unfilled

## Contact Features

Contact Base Material	Brass
Contact Plating Material	Tin

## Dimensions

Wire Size (CMA)	24 – 19 AWG
-----------------	-------------

## Electrical Characteristics

Voltage Rating	48 Vdc
----------------	--------

## Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
--------	--

## Product Type Features

Product Type	Splice
System	PICABOND
Splicing Applications	High Count Straight

## Usage Conditions

552043-2

Operating Temperature -40 – 60 °C

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant